



3DLPrinter-HD 2.0+

3DLPrinter-HD 2.0+ system includes:

- **3DLprinter-HD 2.0+** printer
- Management and printing **Software** 3DL Printer.
- User Manual.
- **Ultrasonic device** (for parts cleaning).
- **UV oven** (for part surface hardening).
- Special pliers in plastic (for manipulating objects).
- Plastic spreader (for cleaning the vat).
- Brush (for the cleaning of the vat).
- Steel scraper (for remove the printed piece).
- Pack of moistened napkins (for lens cleaning).
- Pack of disposable gloves (for part handling).
- Polypropylene tray (for tools cleaning).
- Metallic palette (for resin mixing).
- Hex service key of 2,5 mm.
- Pack of paper sheets useful (for initial zeroing).
- Bubble level tool (for printer leveling).
- 1 Plastic box (empty - useful for cleaning).
- 1 Plastic bottle - containing 300 g of "**RF Resin - CS Red**".
- 1 Plastic bottle (empty – for take the used resin).
- Package containing two **Siligel**.
- Roller (for applying Siligel.)
- 1 Syringe (capacity 60 ml.) without needle (for remove liquid from ultrasonic device)
- 1 Rechargeable air blower (for dry the printed piece)
- 1 Rubber blower (for remove dirt on projector lens)
- 1 Inox filter (for filtering the used resin)
- 1 Spanner -13 mm (to tighten the adjustable feet)
- 1 Pack of paper towels (for cleaning)
- 1 Little bottle of Shampoo (for application of Siligel).

Robot Factory S.r.l. - Via Caltana, 59 - 30035 Mirano VE

Tel - Fax: +39-041-5770270 Mobile: +39-3387159853 - P.IVA: 03654900277

www.robotfactory.it - robot@robotfactory.it

Robot Factory S.r.l. reserves the right to make changes in specifications, materials and accessories without notice. No warranty is provided beyond that attached to the product. Robot Factory S.r.l. assumes no liability for any incidental or consequential, foreseeable or not, caused by misuse of its products.